

# Rittal – The System.

Faster – better – everywhere.



## SV 9340.520 OM adaptors

State: 13.05.2026 (Source: [rittal.com/bg-bg](http://rittal.com/bg-bg))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9340.520 - OM adaptors with spring terminals



## Features

Model No.	SV 9340.520
Design	with spring terminals
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	Chassis: RAL 7035
Rated current max.	32 A
Rated operating voltage	690 V, 3~
For bar systems with centre-to-centre spacing	60 mm
Support rail type	without support frame, 2 x TS 45D
Number of poles	3-pole
Dimensions	Width: 45 mm Height: 208 mm
Connection of round conductors	1.5 - 6 mm <sup>2</sup>
Support rails Qty/height	2 / 10 mm
To fit busbars	Height: 5, 10 mm
Packs of	1 pc(s).
Net weight	0,238 kg
Gross weight	0,266 kg

# Features

---

Copper weight (kg per piece)	0,027
Customs tariff number	85369095
ETIM 9	EC001531
ECLASS 8.0	27370304
Product description	SV OM adaptor, 32 A, 690 V, 3-pole, tension spring clamp 1,5-6 mm <sup>2</sup> , WH: 45x208 mm, support rail 2xTS 45D

---

# Approvals

---

Approvals	ABS DNV Lloyds Register
Explanations	Declaration of conformity Declaration of conformity UK

---