

# Rittal – The System.

Faster – better – everywhere.



## SV 9340.860 Cable set

State: 13.05.2026 (Source: [rittal.com/bg-bg](http://rittal.com/bg-bg))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9340.860 - Cable set for OM adaptors with spring terminal block

Pre-assembled connection cables for individual connection of switchgear.



## Features

Model No.	SV 9340.860
Product description	Pre-assembled connection cables for individual connection of switchgear, top-mounted on OM adaptors with tension spring clamps.
Material	PVC insulation Temperature resistant to 105 °C Wire ends with ultrasonic wire-end compression at both ends
AWG	AWG 12 = 3.31 mm <sup>2</sup> $\times$ 4 mm <sup>2</sup>
Note	AWG = American Wire Gauge
Dimensions	Length: 140 mm
Packs of	15 pc(s).
Net weight	0,075 kg
Gross weight	0,085 kg
Copper weight (kg per piece)	0,003
Customs tariff number	85444290
ETIM 9	EC000839
ECLASS 8.0	27062302
Product description	SV Cable set, AWG 12, L: 140 mm

# Approvals

---

Explanations

Declaration of conformity

Declaration of conformity UK