

Rittal – The System.

Faster – better – everywhere.



SV 9613.000

**Mini-PLS busbar connection
adaptor**

State: 09.05.2026 (Source: rittal.com/bg-bg)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9613.000 - Mini-PLS busbar connection adaptor

Rated current 63 A/1600 A/250 A, cable outlet top/bottom

Features

Model No.	SV 9613.000
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	RAL 7035 Chassis: RAL 9011
Clamping area for laminated copper bars (W x H)	10 x 8 mm
Note	Wire end ferrules should be used with fine wire conductors
Cable outlet	Top/bottom
Rated operating voltage	690 V
Rated current max.	63 A
Dimensions	Width: 54 mm Height: 160 mm
Connection of round conductors	1.5 - 35 mm ²
Packs of	1 pc(s).
Net weight	0,37 kg
Gross weight	0,397 kg
Copper weight (kg per piece)	0,081
Customs tariff number	85369010
ETIM 9	EC001531
ECLASS 8.0	27370304
Product description	SV Mini-PLS busbar connection adaptor, 63 A, 690 V, 3-pole, round conductor connection 1,5-35 mm ² , clamping area WH: 10x8 mm

Approvals

Explanations

Declaration of conformity

Declaration of conformity UK