

Rittal – The System.

Faster – better – everywhere.



SV 9677.700 Component adaptor

State: 21.07.2025 (Source: rittal.com/bg-bg)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9677.700 - Component adaptor clamping attachment

For circuit-breakers from ABB, Eaton, Schneider Electric and Siemens. For bar systems with 185 mm centre-to-centre spacing.

Features

| | |
|---|--|
| Model No. | SV 9677.700 |
| Material | Polyamide Fire protection corresponding to UL 94-V0 |
| Colour | RAL 7035 |
| For bar systems with centre-to-centre spacing | 185 mm |
| Cable outlet | Bottom |
| Installation type | Clamping attachment |
| Number of poles | 3-pole |
| Rated current max. | 1000 A |
| Rated operating voltage | 690 V, 3~ |
| Note | Cable outlet: Switch outlet or as outgoing cable from the switchgear Suitable for the use of switchgear with front screw terminal For mounting on busbar systems with or without cover section |
| Dimensions | Width: 300 mm Height: 652 mm |
| To fit busbars | Height: 10 mm |
| To fit manufacturer (model) | ABB (Tmax T7 - 800 A/1000 A) Eaton (NZM4 - 800 A/1000 A) Schneider Electric (NS - 800 A/1000 A) Siemens (3VA27 - 800 A/1000 A) |
| Packs of | 1 pc(s). |
| Net weight | 13.3 |
| Gross weight | 15.28 |

Features

| | |
|------------------------------|---------------|
| Copper weight (kg per piece) | 7.745 |
| Customs tariff number | 85369095 |
| EAN | 4028177707092 |
| ETIM 9 | EC001531 |
| ECLASS 8.0 | 27370304 |

Approvals

| | |
|--------------|---|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity Declaration of conformity UK |