


Rittal – The System.

Faster – better – everywhere.



SZ 9765.250 Ground plinth

State: 31.07.2025 (Source: [rittal.com/bg-bg](https://www.rittal.com/bg-bg))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 9765.250 - Ground plinth for multifunctional enclosures

Stainless steel ground plinth for multifunctional enclosures.

Features

Model No.	SZ 9765.250
Material	Stainless steel 1.4016 (AISI 430)
Surface finish	Enclosure: Powder-coated, UV-resistant pure polyester
Colour	RAL 7035
Supply includes	Assembly parts
Dimensions	Width: 2,000 mm Height: 660 mm Depth: 500 mm
To fit	Enclosure type: MFG 18
Packs of	1 pc(s).
Net weight	55
Gross weight	70
Customs tariff number	94039910
EAN	4028177686748
ETIM 9	EC000721

Tender text

Ground Plinth for MFC 18

Plinth system for outdoor installation, consisting of Basic housing, and 4x base feet.
Housing and base feet made of 2 mm stainless steel 1.4016.
Completely powder coated in

RAL 7035 pure polyester.

Material: stainless steel 1.4016

Surface: powder coated in RAL 7035, pure polyester

Dimensions: WHT 2000x 600 x 500

Brand: Rittal

Type: ground base for MFC 18 or equivalent

Manufacturer: Rittal GmbH & Co. KG