

# Rittal – The System.

Faster – better – everywhere.



## AE 1005.500

### Wall-mounted AE

State: 2026-01-31 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AE 1005.500 - Wall-mounted AE Stainless steel

Wall-mounted enclosure AE in stainless steel including mounting panel

## Features

|                                      |  |
|--------------------------------------|--|
| Model No.                            | AE 1005.500  |
| Material                             | Housing: Stainless steel<br>Door: Stainless steel, all-round foamed-in PU seal<br>Mounting plate: Carbon steel<br>Stainless steel 1.4404 (AISI 316L) |
| Surface finish                       | Housing and door: Brushed, grain 400, peak-to-valley height<br>< 0.8 µm<br>Mounting panel: Zinc-plated   |
| Supply includes                      | Housing with door(s)<br>Mounting panel<br>Lock: 3 mm double-bit  |
| Protection category NEMA             | NEMA 4X  |
| Protection category IP to EN 60 529  | IP 66  |
| IK code                              | IK08   |
| Dimensions                           | Width: 300 mm<br>Height: 380 mm<br>Depth: 210 mm   |
| Dimensions of mounting plate (W x H) | 275 mm x 334 mm  |
| Number of doors                      | 1  |
| No. of locks                         | 1  |
| Lock                                 | Lock version: Cam<br>No. of locks: 1<br>Lock Insert: 3 mm double-bit<br>Material lock: Stainless steel 1.4404 (AISI 316L)                            |
| Base material                        | Stainless steel 1.4404 (AISI 316L)   |

## Features

---

|                       |               |
|-----------------------|---------------|
| Packaging unit        | 1 pc(s).      |
| Net weight            | 8             |
| Gross weight          | 8.05          |
| Customs tariff number | 94032080      |
| EAN                   | 4028177421271 |
| ETIM 9                | EC000261      |
| ETIM 8                | EC000261      |
| ECLASS 8.0            | 27180101      |

---

## Approvals

---

|              |   |
|--------------|---|
| Approvals    | DNV-GL<br>UL + C-UL (listed)                              |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |

---