

Rittal – The System.

Faster – better – everywhere.



AE 1017.600

Wall-mounted AE

State: 2026-01-13 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))



FRIEDHELM LOH GROUP

AE 1017.600 - Wall-mounted AE Stainless steel

Wall-mounted enclosure AE in stainless steel including mounting panel

Features

Model No.	AE 1017.600
Material	<p>Housing: Stainless steel</p> <p>Door: Stainless steel, all-round foamed-in PU seal</p> <p>Mounting plate: Carbon steel</p> <p>Stainless steel 1.4301 (AISI 304)</p>
Surface finish	<p>Housing and door: Brushed, grain 400, peak-to-valley height < 0.8 µm</p> <p>Mounting panel: Zinc-plated</p>
Supply includes	<p>Housing with door(s)</p> <p>Mounting panel</p> <p>Lock: 3 mm double-bit</p> <p>3-point locking system</p>
Protection category NEMA	NEMA 4X
Protection category IP to EN 60 529	IP 66
IK code	IK08
Dimensions	<p>Width: 800 mm</p> <p>Height: 1,200 mm</p> <p>Depth: 300 mm</p>
Dimensions of mounting plate (W x H)	740 mm x 1,155 mm
Number of doors	1
Lock	<p>Lock version: 3-point locking system</p> <p>No. of locks: 1</p> <p>Lock Insert: 3 mm double-bit</p> <p>Material lock: Stainless steel 1.4301 (AISI 304)</p>
Base material	Stainless steel 1.4301 (AISI 304)
Packaging unit	1 pc(s).

Features

Net weight	57.8
Gross weight	65.16
Customs tariff number	94032080
EAN	4028177000612
E-Number Sweden	E3404426
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

Approvals

Approvals	DNV-GL Lloyds Register of Shipping UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK
