

Rittal – The System.

Faster – better – everywhere.



AE 1017.600 Wall-mounted AE

State: 2025-12-16 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AE 1017.600 - Wall-mounted AE Stainless steel

Wall-mounted enclosure AE in stainless steel including mounting panel

Features

Model No.	AE 1017.600
Material	Housing: Stainless steel Door: Stainless steel, all-round foamed-in PU seal Mounting plate: Carbon steel Stainless steel 1.4301 (AISI 304)
Surface finish	Housing and door: Brushed, grain 400, peak-to-valley height < 0.8 µm Mounting panel: Zinc-plated
Supply includes	Housing with door(s) Mounting panel Lock: 3 mm double-bit 3-point locking system
Protection category NEMA	NEMA 4X
Protection category IP to EN 60 529	IP 66
IK code	IK08
Dimensions	Width: 800 mm Height: 1,200 mm Depth: 300 mm
Dimensions of mounting plate (W x H)	740 mm x 1,155 mm
Number of doors	1
Lock	Lock version: 3-point locking system No. of locks: 1 Lock Insert: 3 mm double-bit Material lock: Stainless steel 1.4301 (AISI 304)
Base material	Stainless steel 1.4301 (AISI 304)
Packaging unit	1 pc(s).

Features

Net weight	57.8
Gross weight	65.16
Customs tariff number	94032080
EAN	4028177000612
E-Number Sweden	E3404426
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

Approvals

Approvals	DNV-GL Lloyds Register of Shipping UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK