## Rittal – The System.

Faster – better – everywhere.





# AE 1019.500 Wall-mounted AE

State: 2025-11-29 (Source: rittal.com/ca-en)



### AE 1019.500 - Wall-mounted AE Stainless steel

Wall-mounted enclosure AE in stainless steel including mounting panel

#### **Features**

Model No.	AE 1019.500
Material	Housing: Stainless steel
	Door: Stainless steel, all-round foamed-in PU seal
	Mounting plate: Carbon steel
	Stainless steel 1.4404 (AISI 316L)
Surface finish	Housing and door: Brushed, grain 400, peak-to-valley height
	< 0.8 μm
	Mounting panel: Zinc-plated
Supply includes	Housing with door(s)
	Mounting panel
	Lock: 3 mm double-bit
	3-point locking system
Protection category NEMA	NEMA 12
Protection category IP to EN 60 529	IP 55
IK code	IK08
Dimensions	Width: 1,000 mm
	Height: 1,200 mm
	Depth: 300 mm
Dimensions of mounting plate (W x H)	940 mm x 1,155 mm
Number of doors	2
Lock	Lock version: 3-point locking system
	No. of locks: 1
	Lock Insert: 3 mm double-bit
	Material lock: Stainless steel 1.4301 (AISI 304)
Base material	Stainless steel 1.4404 (AISI 316L)
Packaging unit	1 pc(s).

© Rittal 2025

#### **Features**

Net weight	76.4
Gross weight	79.5
Customs tariff number	94032080
EAN	4028177421394
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

# Approvals

DNV-GL UL + C-UL (listed)
Declaration of conformity  Declaration of conformity UK

© Rittal 2025 3