

# Rittal – The System.

Faster – better – everywhere.



## AE 1019.500 Wall-mounted AE

State: 2026-04-18 (Source: [rittal.com/ca-en](http://rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AE 1019.500 - Wall-mounted AE Stainless steel

Wall-mounted enclosure AE in stainless steel including mounting panel

## Features

|                                      |  |
|--------------------------------------|--|
| Model No.                            | AE 1019.500  |
| Material                             | Housing: Stainless steel<br>Door: Stainless steel, all-round foamed-in PU seal<br>Mounting plate: Carbon steel<br>Stainless steel 1.4404 (AISI 316L) |
| Surface finish                       | Housing and door: Brushed, grain 400, peak-to-valley height < 0.8 µm<br>Mounting panel: Zinc-plated  |
| Supply includes                      | Housing with door(s)<br>Mounting panel<br>Lock: 3 mm double-bit<br>3-point locking system  |
| Protection category NEMA             | NEMA 12  |
| Protection category IP to EN 60529   | IP 55  |
| IK code                              | IK08   |
| Dimensions                           | Width: 1,000 mm<br>Height: 1,200 mm<br>Depth: 300 mm   |
| Dimensions of mounting plate (W x H) | 940 mm x 1,155 mm  |
| Number of doors                      | 2  |
| Lock                                 | Lock version: 3-point locking system<br>No. of locks: 1<br>Lock Insert: 3 mm double-bit<br>Material lock: Stainless steel 1.4301 (AISI 304)          |
| Base material                        | Stainless steel 1.4404 (AISI 316L)   |
| Packaging unit                       | 1 pc(s).   |

# Features

---

|                       |   |
|-----------------------|---|
| Net weight            | 76.4 kg   |
| Gross weight          | 79.5 kg   |
| Customs tariff number | 94032080  |
| ETIM 9                | EC000261  |
| ETIM 8                | EC000261  |
| ECLASS 8.0            | 27180101  |
| Product description   | AE Compact enclosure, WHD: 1000x1200x300 mm, Stainless steel 1.4404, with mounting plate, two-door, 3-point lock system |

# Approvals

---

|              |   |
|--------------|---|
| Approvals    | DNV-GL<br>UL + C-UL (listed)                              |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |