Rittal – The System.

Faster – better – everywhere.





AE 1019.600 Wall-mounted AE

State: 2025-10-29 (Source: rittal.com/ca-en)



AE 1019.600 - Wall-mounted AE Stainless steel

Wall-mounted enclosure AE in stainless steel including mounting panel

Features

Model No.	AE 1019.600
Material	Housing: Stainless steel
	Door: Stainless steel, all-round foamed-in PU seal
	Mounting plate: Carbon steel
	Stainless steel 1.4301 (AISI 304)
Surface finish	Housing and door: Brushed, grain 400, peak-to-valley height
	< 0.8 μm
	Mounting panel: Zinc-plated
Supply includes	Housing with door(s)
	Mounting panel
	Lock: 3 mm double-bit
	3-point locking system
Protection category NEMA	NEMA 12
Protection category IP to EN 60 529	IP 55
IK code	IK08
Dimensions	Width: 1,000 mm
	Height: 1,200 mm
	Depth: 300 mm
Dimensions of mounting plate (W x H)	940 mm x 1,155 mm
Number of doors	2
Lock	Lock version: 3-point locking system
	No. of locks: 1
	Lock Insert: 3 mm double-bit
	Material lock: Stainless steel 1.4301 (AISI 304)
	Stainless steel 1.4301 (AISI 304)
Base material	

© Rittal 2025

Features

71.4
79.5
94032080
4028177000698
E3404430
EC000261
EC000261
27180101

Approvals

Approvals	DNV-GL Lloyds Register of Shipping UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK

© Rittal 2025 3