



# AE 1019.600

## Wall-mounted AE

State: 2026-05-09 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AE 1019.600 - Wall-mounted AE Stainless steel

Wall-mounted enclosure AE in stainless steel including mounting panel

## Features

Model No.	AE 1019.600
Material	Housing: Stainless steel Door: Stainless steel, all-round foamed-in PU seal Mounting plate: Carbon steel Stainless steel 1.4301 (AISI 304)
Surface finish	Housing and door: Brushed, grain 400, peak-to-valley height < 0.8 µm Mounting panel: Zinc-plated
Supply includes	Housing with door(s) Mounting panel Lock: 3 mm double-bit 3-point locking system
Protection category NEMA	NEMA 12
Protection category IP to EN 60529	IP 55
IK code	IK08
Dimensions	Width: 1,000 mm Height: 1,200 mm Depth: 300 mm
Dimensions of mounting plate (W x H)	940 mm x 1,155 mm
Number of doors	2
Lock	Lock version: 3-point locking system No. of locks: 1 Lock Insert: 3 mm double-bit Material lock: Stainless steel 1.4301 (AISI 304)
Base material	Stainless steel 1.4301 (AISI 304)
Packaging unit	1 pc(s).

# Features

---

Net weight	71.4 kg
Gross weight	79.5 kg
Customs tariff number	94032080
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101
Product description	AE Compact enclosure, WHD: 1000x1200x300 mm, Stainless steel 1.4301, with mounting plate, two-door, 3-point lock system

# Approvals

---

Approvals	DNV Lloyds Register UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK