

Rittal – The System.

Faster – better – everywhere.



AE 1030.500 Wall-mounted AE

State: 2026-04-16 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AE 1030.500 - Wall-mounted AE

Housing with door of carbon steel, spray-finished with mounting plate and gland panel in the base.

Features

| | |
|--------------------------------------|--|
| Model No. | AE 1030.500 |
| Material | Housing: Carbon steel Door: Carbon steel, all-round foamed-in PU seal |
| Surface finish | Housing and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting panel: Zinc-plated |
| Color | RAL 7035 |
| Supply includes | Housing with hinged door(s), of all-round solid construction Flange (gland) plate(s) in enclosure base Mounting panel Lock: 3 mm double-bit |
| Protection category NEMA | NEMA 4 |
| Protection category IP to EN 60529 | IP 66 |
| IK code | IK08 |
| Dimensions | Width: 380 mm Height: 300 mm Depth: 155 mm |
| Material thickness - door | 1.5 mm |
| Material thickness - enclosure | 1.38 mm |
| Material thickness – mounting plate | 2 mm |
| Dimensions of mounting plate (W x H) | 334 mm x 275 mm |
| Number of doors | 1 |
| Interchangeable door catch | Yes |

Features

| | |
|-----------------------|---|
| No. of locks | 1 |
| Lock | Lock version: Cam No. of locks: 1 Lock Insert: 3 mm double-bit |
| Gland plate | Size: 3 Qty.: 1 |
| Base material | Carbon steel |
| Packaging unit | 1 pc(s). |
| Gross weight | 7.4 kg |
| Customs tariff number | 94032080 |
| ECLASS 8.0 | 27180101 |
| Product description | AE Compact enclosure, WHD: 380x300x155 mm, Sheet steel, with mounting plate, single-door, with one cam lock |

Approvals

| | |
|--------------|---|
| Approvals | DNV-GL Lloyds Register of Shipping UL + C-UL (listed) |
| Explanations | Declaration of conformity Declaration of conformity UK |