Rittal – The System.

Faster – better – everywhere.





AE 1060.500 Wall-mounted AE

State: 2025-11-16 (Source: rittal.com/ca-en)



AE 1060.500 - Wall-mounted AE

Housing with door of carbon steel, spray-finished with mounting plate and gland panel in the base.

Features

| Model No. | AE 1060.500 |
|--|---|
| Material | Housing: Carbon steel Door: Carbon steel, all-round foamed-in PU seal |
| Surface finish | Housing and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting panel: Zinc-plated |
| Color | RAL 7035 |
| Supply includes | Housing with hinged door(s), of all-round solid construction Flange (gland) plate(s) in enclosure base Mounting panel Lock: 3 mm double-bit |
| Protection category NEMA | NEMA 4 |
| Protection category IP to EN 60 529 | IP 66 |
| IK code | IK08 |
| Dimensions | Width: 600 mm Height: 600 mm Depth: 210 mm |
| Material thickness - door | 1.75 mm |
| Material thickness - enclosure | 1.38 mm |
| Material thickness – mounting plate | 2.5 mm |
| Dimensions of mounting plate (W x H) | 549 mm x 570 mm |
| Number of doors | 1 |
| Interchangeable door catch | Yes |

© Rittal 2025

2

Features

| No. of locks | 2 |
|-----------------------|------------------------------|
| Lock | Lock version: Cam |
| | No. of locks: 2 |
| | Lock Insert: 3 mm double-bit |
| Gland plate | Size: 5 |
| | Qty.: 1 |
| Base material | Carbon steel |
| Packaging unit | 1 pc(s). |
| Net weight | 20.418 |
| Gross weight | 22.5 |
| Customs tariff number | 94032080 |
| EAN | 4028177252103 |
| E-Number Sweden | E3404614 |
| ETIM 9 | EC000261 |
| ETIM 8 | EC000261 |
| ECLASS 8.0 | 27180101 |
| | |

Approvals

| Approvals | DNV-GL |
|--------------|---------------------------------|
| | Lloyds Register of Shipping |
| | III I C III (listed) |
| | UL + C-UL (listed) |
| | |
| Explanations | Declaration of conformity |
| | Declaration of conformation III |
| | Declaration of conformity UK |

© Rittal 2025 3