## Rittal – The System.

Faster – better – everywhere.





# AE 1260.500 Wall-mounted AE

State: 2025-11-15 (Source: rittal.com/ca-en)



## AE 1260.500 - Wall-mounted AE

Housing with door of carbon steel, spray-finished with mounting plate and gland panel in the base.

#### **Features**

1260.500
using: Carbon steel or: Carbon steel, all-round foamed-in PU seal
using and door: Dipcoat primed, powder-coated on the outside, tured paint ounting panel: Zinc-plated
L 7035
using with hinged door(s), of all-round solid construction nge (gland) plate(s) in enclosure base unting panel ck: 3 mm double-bit oint locking system
MA 4
56
18
dth: 600 mm ight: 1,200 mm oth: 300 mm
nm
mm
nm
0 mm x 1,155 mm

© Rittal 2025

## Features

Interchangeable door catch	Yes
Lock	Lock version: 3-point locking system No. of locks: 1 Lock Insert: 3 mm double-bit
Gland plate	Size: 5 Qty.: 1
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	49.4
Gross weight	51
Customs tariff number	94032080
EAN	4028177252448
E-Number Sweden	E3404625
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

## Approvals

Approvals	Bureau Veritas
	DNV-GL
	Lloyds Register of Shipping
	UL + C-UL (listed)
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3