

# Rittal – The System.

Faster – better – everywhere.



## WM 1350.250

## WM wall-mounted enclosure

State: 2024-05-19 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# WM 1350.250 - WM wall-mounted enclosure single-door

These single door wallmount enclosures can be used for virtually any application. The WM series ensures NEMA protection through a secure locking system, foamed-in-place gasket, and knife-edge sealing surface. Features include a cold rolled steel body and door, and a zinc plated mounting panel.



## Features

Model No.	WM 1350.250
Material	Door: Carbon steel, all-round foamed-in PU seal Housing: Carbon steel
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting plate: Zinc-plated
Color	RAL 7035
Supply includes	Housing with door(s) Door hinged on left Mounting plate Rear wall mounting holes Quarter turn latch with slotted head insert
Dimensions	Width: 500 mm Height: 500 mm Depth: 300 mm
Dimensions of mounting plate (W x H)	449 mm x 470 mm
Protection category NEMA	NEMA 1, 3R, 4, 12
Material thickness - door	1.5 mm

# Features

Material thickness - enclosure	1.5 mm
Material thickness – mounting plate	2.5 mm
Packaging unit	1 pc(s).
Weight/packaging unit	20 kg
Customs tariff number	7326908688
EAN	4028177532731
UPC-Code	83114

# Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity