

Rittal – The System.

Faster – better – everywhere.



KS 1434.500

KS Plastic Enclosures

State: 2026-06-21 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



KS 1434.500 - KS Plastic Enclosures

Wall-mounted housing with door of fiberglass-reinforced, non-saturated polyester, with mounting plate. Optionally with or without glazed door. Protection category IP 56 or IP 66. Infinite mounting plate depth adjustment, thanks to multiple mounting levels in the enclosure. Flexible interior door configuration using press-fitted mounting bosses in the door. High stability thanks to use of fibre-glass reinforced plastic.

Features

Model No.	KS 1434.500
Version	without viewing window
Material	Housing and door: Fiberglass-reinforced unsaturated polyester Door: All-round foamed-in PU seal Mounting plate: Carbon steel Viewing window: Glazed acrylic, 3.0 mm with all-round rubber cable clamp strip
Surface finish	Housing and door: Dyed plastic with no after-treatment Mounting panel: Zinc-plated
Color	Similar to RAL 7035
Supply includes	Housing with hinged door, of all-round solid construction, 3 mm double-bit lock Mounting panel Twin seal on the top and bottom edges of the door as integral rain protection strip Press-fitted C sections at the sides for infinitely variable mounting plate depth adjustment
Note	Under the influence of long-term UV radiation (sunlight) in conjunction with wind and rain, the surface finish may become visually impaired. This does not affect the protection of the installed electrical components in any way. If the enclosures cannot be protected from UV radiation, we recommend that they should be painted with a PUR paint. Permissible ambient temperature -30 °C... +75 °C.
Protection category NEMA	NEMA 4X

Features

Protection category IP to EN 60529	IP 66
IK code	IK08
Dimensions	Width: 300 mm Height: 400 mm Depth: 200 mm
Material thickness – mounting plate	2 mm
Dimensions of mounting plate (W x H)	245 mm x 350 mm
Number of doors	1
Interchangeable door catch	Yes
No. of locks	2
Lock	Lock version: Cam No. of locks: 2 Lock Insert: 3 mm double-bit
Base material	Plastic
Packaging unit	1 pc(s).
Net weight	5.716 kg
Gross weight	6.017 kg
Customs tariff number	94037000
ECLASS 8.0	27180101
Product description	KS Plastic enclosure, WHD: 300x400x200 mm, Fibreglass-reinforced unsaturated polyester, with mounting plate, with door

Approvals

Approvals	Bureau Veritas TÜV
-----------	-----------------------

Approvals

Explanations

Declaration of conformity

Declaration of conformity UK