## Rittal – The System.

Faster – better – everywhere.





# KL 1502.510 KL Terminal Boxes

State: 2025-11-07 (Source: rittal.com/ca-en)



## KL 1502.510 - KL Terminal Boxes without gland plate

Spray-finished housing with sheet steel cover, without gland panel. Protection category IP 66.

#### **Features**

Model No.	KL 1502.510	
Material	Housing: Carbon steel Cover: Carbon steel, all-round foamed-in PU seal	
Surface finish	Housing and cover: Dipcoat primed, powder-coated on the outside, textured paint	
Color	RAL 7035	
Supply includes	Housing with cover Quick-release fasteners including plastic bushings	
Protection category NEMA	NEMA 4	
Protection category IP to EN 60 529	IP 66	
IK code	IK08	
Dimensions	Width: 200 mm Height: 200 mm Depth: 120 mm	
Material thickness - cover	1.25 mm	
Material thickness - enclosure	1.25 mm	
Base material	Carbon steel	
Packaging unit	1 pc(s).	
Net weight	1.968	
Gross weight	2.12	
Customs tariff number	73269098	
EAN	4028177251144	
E-Number Sweden	E3404664	

© Rittal 2025

### Features

ETIM 9	EC000261	
ETIM 8	EC000261	
ECLASS 8.0	27180101	

## **Approvals**

Approvals	Bureau Veritas
	DNV-GL
	Lloyds Register of Shipping
	UL + C-UL (listed)
Explanations	Manufacturer's declaration
	Declaration of conformity UK

© Rittal 2025 3