

Rittal – The System.

Faster – better – everywhere.



KL 1507.510

KL Terminal Boxes

State: 2025-09-08 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



KL 1507.510 - KL Terminal Boxes without gland plate

Spray-finished housing with sheet steel cover, without gland panel. Protection category IP 66.

Features

| | |
|-------------------------------------|---|
| Model No. | KL 1507.510 |
| Material | Housing: Carbon steel Cover: Carbon steel, all-round foamed-in PU seal |
| Surface finish | Housing and cover: Dipcoat primed, powder-coated on the outside, textured paint |
| Color | RAL 7035 |
| Supply includes | Housing with cover Quick-release fasteners including plastic bushings |
| Protection category NEMA | NEMA 4 |
| Protection category IP to EN 60 529 | IP 66 |
| IK code | IK08 |
| Dimensions | Width: 300 mm Height: 300 mm Depth: 120 mm |
| Material thickness - cover | 1.25 mm |
| Material thickness - enclosure | 1.38 mm |
| Base material | Carbon steel |
| Packaging unit | 1 pc(s). |
| Net weight | 3.745 |
| Gross weight | 3.97 |
| Customs tariff number | 73269098 |
| EAN | 4028177251199 |
| E-Number Sweden | E3404669 |

Features

| | |
|------------|----------|
| ECLASS 8.0 | 27180101 |
|------------|----------|

Approvals

| | |
|--------------|---|
| Approvals | Bureau Veritas DNV-GL Lloyds Register of Shipping UL + C-UL (listed) |
| Explanations | Manufacturer's declaration Declaration of conformity UK |