Rittal – The System.

Faster – better – everywhere.





KL 1511.510 KL Terminal Boxes

State: 2025-11-08 (Source: rittal.com/ca-en)



KL 1511.510 - KL Terminal Boxes without gland plate

Spray-finished housing with sheet steel cover, without gland panel. Protection category IP 66.



Features

KL 1511.510
Housing: Carbon steel
Cover: Carbon steel, all-round foamed-in PU seal
Housing and cover: Dipcoat primed, powder-coated on the outside, textured paint
RAL 7035
Housing with cover
Quick-release fasteners including plastic bushings
NEMA 4
IP 66
IK08
Width: 400 mm
Height: 400 mm
Depth: 120 mm
1.25 mm
1.38 mm
Carbon steel
1 pc(s).
5.832

© Rittal 2025

Features

Gross weight	6.139
Customs tariff number	73269098
EAN	4028177251236
E-Number Sweden	E3404673
ECLASS 8.0	27180101

Approvals

Approvals	Bureau Veritas
	DNV-GL
	Lloyds Register of Shipping
	UL + C-UL (listed)
Explanations	Manufacturer's declaration
	Declaration of conformity UK

© Rittal 2025 3