

**Rittal – The System.**

Faster – better – everywhere.



**KL 1516.510**

**KL Terminal Boxes**

State: 2026-02-05 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# KL 1516.510 - KL Terminal Boxes without gland plate

Spray-finished housing with sheet steel cover, without gland panel. Protection category IP 66.



## Features

Model No.	KL 1516.510
Material	Housing: Carbon steel Cover: Carbon steel, all-round foamed-in PU seal
Surface finish	Housing and cover: Dipcoat primed, powder-coated on the outside, textured paint
Color	RAL 7035
Supply includes	Housing with cover Quick-release fasteners including plastic bushings
Protection category NEMA	NEMA 4
Protection category IP to EN 60 529	IP 66
IK code	IK08
Dimensions	Width: 200 mm Height: 200 mm Depth: 80 mm
Material thickness - cover	1.25 mm
Material thickness - enclosure	1.25 mm
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	1.586

# Features

---

Gross weight 1.786

Customs tariff number 73269098

EAN 4028177251281

E-Number Sweden E3404678

ETIM 9 EC000261

ETIM 8 EC000261

ECLASS 8.0 27180101

# Approvals

---

Approvals Bureau Veritas  
DNV-GL  
Lloyds Register of Shipping  
UL + C-UL (listed)

Explanations Manufacturer's declaration  
Declaration of conformity UK