## Rittal – The System.

Faster – better – everywhere.





# KL 1522.010 KL Terminal Boxes

State: 2025-11-12 (Source: rittal.com/ca-en)



## KL 1522.010 - KL Terminal Boxes Stainless steel

Terminal box of stainless steel 1.4301, (AISI 304). Protection category IP 66.

#### **Features**

Model No.	KL 1522.010
Material	Housing: Stainless steel 1.4301 (AISI 304) Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in PU seal
Surface finish	Housing and cover: Brushed, grain 180
Supply includes	Housing with cover Quick-release fasteners including plastic bushings
Protection category NEMA	NEMA 4X
Protection category IP to EN 60 529	IP 66
IK code	IK08
Dimensions	Width: 300 mm Height: 150 mm Depth: 80 mm
Material thickness - cover	1.25 mm
Material thickness - enclosure	1.25 mm
Lock	No. of locks: 4
Base material	Stainless steel 1.4301 (AISI 304)
Packaging unit	1 pc(s).
Net weight	1.673
Gross weight	1.94
Customs tariff number	84879090
EAN	4028177008465
E-Number Sweden	E3404364
ETIM 9	EC000261

© Rittal 2025

## Features

ETIM 8	EC000261
ECLASS 8.0	27180101

# **Approvals**

Approvals	Bureau Veritas
	DNV-GL
	Lloyds Register of Shipping
	UL + C-UL (listed)
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3