

Rittal – The System.

Faster – better – everywhere.



KL 1525.010

KL Terminal Boxes

State: 2025-07-17 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



KL 1525.010 - KL Terminal Boxes Stainless steel

Terminal box of stainless steel 1.4301, (AISI 304). Protection category IP 66.

Features

| | |
|------------------------------------|---|
| Model No. | KL 1525.010 |
| Material | Housing: Stainless steel 1.4301 (AISI 304) Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in PU seal |
| Surface finish | Housing and cover: Brushed, grain 180 |
| Supply includes | Housing with cover Quick-release fasteners including plastic bushings |
| Protection category NEMA | NEMA 4X |
| Protection category IP to EN 60529 | IP 66 |
| IK code | IK08 |
| Dimensions | Width: 400 mm Height: 200 mm Depth: 120 mm |
| Material thickness - cover | 1.25 mm |
| Material thickness - enclosure | 1.25 mm |
| Lock | No. of locks: 4 |
| Base material | Stainless steel 1.4301 (AISI 304) |
| Packaging unit | 1 pc(s). |
| Net weight | 3 |
| Gross weight | 3.46 |
| Customs tariff number | 84879090 |
| EAN | 4028177008526 |
| E-Number Sweden | E3404367 |
| ETIM 9 | EC000261 |

Features

| | |
|------------|----------|
| ETIM 8 | EC000261 |
| ECLASS 8.0 | 27180101 |

Approvals

| | |
|--------------|---|
| Approvals | Bureau Veritas DNV-GL Lloyds Register of Shipping UL + C-UL (listed) |
| Explanations | Declaration of conformity Declaration of conformity UK |