

Rittal – The System.

Faster – better – everywhere.



KL 1530.010

KL Terminal Boxes

State: 2026-01-30 (Source: rittal.com/ca-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

KL 1530.010 - KL Terminal Boxes Stainless steel

Terminal box of stainless steel 1.4301, (AISI 304). Protection category IP 66.

Features

Model No.	KL 1530.010
Material	Housing: Stainless steel 1.4301 (AISI 304) Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in PU seal
Surface finish	Housing and cover: Brushed, grain 180
Supply includes	Housing with cover Quick-release fasteners including plastic bushings
Protection category NEMA	NEMA 4X
Protection category IP to EN 60 529	IP 66
IK code	IK08
Dimensions	Width: 400 mm Height: 300 mm Depth: 120 mm
Material thickness - cover	1.25 mm
Material thickness - enclosure	1.25 mm
Lock	No. of locks: 4
Base material	Stainless steel 1.4301 (AISI 304)
Packaging unit	1 pc(s).
Net weight	4.5
Gross weight	4.6
Customs tariff number	84879090
EAN	4028177663350
E-Number Sweden	E3404381
ETIM 9	EC000261

Features

ETIM 8 EC000261

ECLASS 8.0 27180101

Approvals

Approvals Bureau Veritas
DNV-GL
UL + C-UL (listed)

Explanations Declaration of conformity
Declaration of conformity UK