

Rittal – The System.

Faster – better – everywhere.



KX 1551.000

E-box KX, carbon steel

State: 2025-07-27 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



KX 1551.000 - E-box KX, carbon steel

The small enclosure KX, E-Box KX, carbon steel offers remarkable ease of assembly and flexibility when selecting lock systems.



Features

Model No.	KX 1551.000
Product description	The small enclosure KX, E-Box KX, carbon steel offers remarkable ease of assembly and flexibility when selecting lock systems.
Material	Housing: Carbon steel Door: Carbon steel, all-round foamed-in PU seal
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting panel: Zinc-plated
Color	RAL 7035
Supply includes	Housing with door Mounting panel Cam lock with 3 mm double-bit insert 180° hinge
Protection category NEMA	NEMA 1 NEMA 3R NEMA 4 NEMA 12
Protection category IP to EN 60529	IP 66

Features

Type rating according to UL 50E	Type 1 Type 3R Type 4 Type 12
IK code	IK08
Dimensions	Width: 150 mm Height: 150 mm Depth: 80 mm
Dimensions of mounting plate (W x H)	125 mm x 135 mm
Material thickness - enclosure	1.25 mm
Material thickness - door	1.25 mm
Material thickness – mounting plate	2 mm
Lock	No. of locks: 1
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	1.313
Gross weight	1.485
PCF/VE (cradle-to-gate)	5.9 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94032080
EAN	4028177816534
E-Number Sweden	E3465219
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

Approvals

Approvals	Bureau Veritas DNV-GL Lloyds Register of Shipping UL + C-UL (listed)
Certificates	Protection category
Explanations	Manufacturer's declaration Declaration of conformity Declaration of conformity UK PCF-declaration