

Rittal – The System.

Faster – better – everywhere.



BG 1558.010

BG Bus Housings

State: 2026-02-13 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))

BG 1558.010 - BG Bus Housings Stainless steel

Bus housing of stainless steel 1.4301, (AISI 304), incl. 180° hinge. Protection category IP 66.

Features

| | |
|-------------------------------------|---|
| Model No. | BG 1558.010 |
| Material | Housing: Stainless steel 1.4301 (AISI 304) Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in PU seal 180° hinges: Die-cast zinc |
| Surface finish | Housing and cover: Brushed, grain 240 180° hinges: Chrome-plated |
| Supply includes | Housing with cover 180° hinges (2 pcs) Support rail TH 35/7.5 Quick-release fasteners including plastic bushings |
| Protection category NEMA | NEMA 4X |
| Protection category IP to EN 60 529 | IP 66 |
| Dimensions | Width: 400 mm Height: 200 mm Depth: 123 mm |
| Material thickness - enclosure | 1.5 mm |
| Material thickness - door | 1.25 mm |
| Position door catch | bottom |
| Number of support rails | 1 |
| Lock | Lock version: Quick-release fasteners including plastic bushings No. of locks: 2 |
| Base material | Stainless steel 1.4301 (AISI 304) |
| Packaging unit | 1 pc(s). |
| Net weight | 3.92 |
| Gross weight | 4.12 |

Features

| | |
|-----------------------|---------------|
| Customs tariff number | 94032080 |
| EAN | 4028177009912 |
| ETIM 9 | EC000261 |
| ETIM 8 | EC000261 |
| ECLASS 8.0 | 27180101 |

Approvals

| | |
|--------------|---|
| Approvals | Lloyds Register of Shipping UL + C-UL (listed) |
| Explanations | Declaration of conformity Declaration of conformity UK |
