Rittal – The System.

Faster – better – everywhere.





BG 1559.010 BG Bus Housings

State: 2025-11-03 (Source: rittal.com/ca-en)



BG 1559.010 - BG Bus Housings Stainless steel

Bus housing of stainless steel 1.4301, (AISI 304), incl. 180° hinge. Protection category IP 66.

Features

Model No.	BG 1559.010
Material	Housing: Stainless steel 1.4301 (AISI 304) Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in PU sea 180° hinges: Die-cast zinc
Surface finish	Housing and cover: Brushed, grain 240 180° hinges: Chrome-plated
Supply includes	Housing with cover 180° hinges (2 pcs) Support rail TH 35/7.5 Quick-release fasteners including plastic bushings
Protection category NEMA	NEMA 4X
Protection category IP to EN 60 529	IP 66
Dimensions	Width: 600 mm Height: 200 mm Depth: 123 mm
Material thickness - enclosure	1.5 mm
Material thickness - door	1.25 mm
Position door catch	bottom
Number of support rails	1
Lock	Lock version: Quick-release fasteners including plastic bushings No. of locks: 3
Base material	Stainless steel 1.4301 (AISI 304)
Packaging unit	1 pc(s).
Net weight	5.653
Gross weight	5.95

© Rittal 2025

Features

Customs tariff number	94032080
EAN	4028177009950
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

Approvals

Approvals	Lloyds Register of Shipping UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK

© Rittal 2025 3