### Rittal – The System.

Faster - better - everywhere.





## KL 1581.000 Plastic cable gland plates

State: 2025-11-23 (Source: rittal.com/ca-en)



# KL 1581.000 - Plastic cable gland plates with PG knockouts

With pre-punched PG holes for cable glands.



#### **Features**

Model No.	KL 1581.000
Product description	With pre-punched PG holes for cable glands. Use with standard flange plate seal.
Material	ABS
Color	RAL 7035
Note	The assignment of the flange plate size can be found on the respective housings
No. of metric knockouts	12
Number x PG diameter	12 x 13.5
Dimensions	Width: 220 mm
	Depth: 90 mm
Suitable for	Enclosure type: KL
Gland plate	Size: 2
Operating temperature range	-40 °C70 °C
Protection category IP to EN 60 529	IP 55 if correctly installed
Number knockouts	12
Packaging unit	5 pc(s).

© Rittal 2025

### **Features**

Net weight	0.505
Gross weight	0.604
Customs tariff number	73079100
EAN	4028177010888
E-Number Sweden	E3404715
ETIM 9	EC000211
ETIM 8	EC000211
ECLASS 8.0	27142421

© Rittal 2025 3