

Rittal – The System.

Faster – better – everywhere.



SZ 1581.100

Metal gland plate

State: 2026-02-04 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))



SZ 1581.100 - Metal gland plate with metric knockouts

Simply knock out the holes for the cable glands with a screwdriver. Protection category IP 66 is achieved when mounting in the usual position at the bottom.

Features

Model No.	SZ 1581.100
Product description	Simply knock out the holes for the cable glands with a screwdriver.
Material	Carbon steel
Color	RAL 7035
Note	The assignment of the flange plate size can be found on the respective housings
No. of metric knockouts	12 x M20
Dimensions	Width: 221 mm Depth: 90 mm
Suitable for	Enclosure type: KL
Gland plate	Size: 2
Protection category IP to EN 60 529	IP66 when mounting in the usual position at the bottom
Number knockouts	12
Metric diameter	M20
Packaging unit	1 pc(s).
Net weight	0.23
Gross weight	0.25
Customs tariff number	73079100
EAN	4028177390843
E-Number Sweden	E3404794
ETIM 9	EC000211
ETIM 8	EC000211

Features

ECLASS 8.0

27142421