

# Rittal – The System.

Faster – better – everywhere.



# SZ 1581.100

## Metal gland plate

State: 2026-05-22 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 1581.100 - Metal gland plate with metric knockouts

Simply knock out the holes for the cable glands with a screwdriver. Protection category IP 66 is achieved when mounting in the usual position at the bottom.

## Features

Model No.	SZ 1581.100
Product description	Simply knock out the holes for the cable glands with a screwdriver.
Material	Carbon steel
Color	RAL 7035
Note	The assignment of the flange plate size can be found on the respective housings
No. of metric knockouts	12 x M20
Dimensions	Width: 221 mm Depth: 90 mm
Suitable for	Enclosure type: KL
Gland plate	Size: 2
Protection category IP to EN 60529	IP66 when mounting in the usual position at the bottom
Packaging unit	1 pc(s).
Net weight	0.23 kg
Gross weight	0.25 kg
Customs tariff number	73079100
ETIM 9	EC000211
ETIM 8	EC000211
ECLASS 8.0	27142421
Product description	SZ Metal gland plate, with metric knock-outs, WD: 221x90 mm, size: 2