

Rittal – The System.

Faster – better – everywhere.



SZ 1581.200

Metal gland plate

State: 2025-08-24 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 1581.200 - Metal gland plate with metric knockouts

Simply knock out the holes for the cable glands with a screwdriver. Protection category IP 66 is achieved when mounting in the usual position at the bottom.

Features

| | |
|-------------------------------------|--|
| Model No. | SZ 1581.200 |
| Product description | Simply knock out the holes for the cable glands with a screwdriver. |
| Material | Carbon steel |
| Color | RAL 7035 |
| Note | The assignment of the flange plate size can be found on the respective housings |
| No. of metric knockouts | 12 x M20 |
| Dimensions | Width: 220 mm Depth: 90 mm |
| Suitable for | Enclosure type: KX |
| Protection category IP to EN 60 529 | IP 55 if correctly installed |
| Type rating according to UL 50E | Type 1 Type 12K |
| Number knockouts | 12 |
| Metric diameter | M20 |
| Packaging unit | 1 pc(s). |
| Net weight | 0.23 |
| Gross weight | 0.24 |
| PCF/VE (cradle-to-gate) | 1.2 kg CO2 eq (Cat B) |
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number | 73079100 |

Features

| | |
|-----------------|---------------|
| EAN | 4028177940536 |
| E-Number Sweden | E3465317 |
| ETIM 9 | EC000211 |
| ETIM 8 | EC000211 |
| ECLASS 8.0 | 27142421 |

Approvals

| | |
|-----------|------------------|
| Approvals | UL + C-UL - FTTA |
|-----------|------------------|