

Rittal – The System.

Faster – better – everywhere.



SZ 1581.200

Metal gland plate

State: 2026-01-19 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 1581.200 - Metal gland plate with metric knockouts

Simply knock out the holes for the cable glands with a screwdriver. Protection category IP 66 is achieved when mounting in the usual position at the bottom.

Features

Model No.	SZ 1581.200
Product description	Simply knock out the holes for the cable glands with a screwdriver.
Material	Carbon steel
Color	RAL 7035
Note	The assignment of the flange plate size can be found on the respective housings
No. of metric knockouts	12 x M20
Dimensions	Width: 220 mm Depth: 90 mm
Suitable for	Enclosure type: KX
Protection category IP to EN 60 529	IP 55 if correctly installed
Type rating according to UL 50E	Type 1 Type 12K
Number knockouts	12
Metric diameter	M20
Packaging unit	1 pc(s).
Net weight	0.23
Gross weight	0.24
PCF/VE (cradle-to-gate)	1.2 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	73079100

Features

EAN	4028177940536
E-Number Sweden	E3465317
ETIM 9	EC000211
ETIM 8	EC000211
ECLASS 8.0	27142421

Approvals

Approvals	UL + C-UL - FTTA
-----------	------------------