Rittal – The System.

Faster - better - everywhere.






KL 1582.000 Plastic cable gland plates

State: 2025-11-23 (Source: rittal.com/ca-en)



KL 1582.000 - Plastic cable gland plates with PG knockouts

With pre-punched PG holes for cable glands.



Features

Model No.	KL 1582.000
Product description	With pre-punched PG holes for cable glands. Use with standard flange plate seal.
Material	ABS
Color	RAL 7035
Note	The assignment of the flange plate size can be found on the respective housings
No. of metric knockouts	6 2 2
Number x PG diameter	6 x 13.5 2 x 16 2 x 21
Dimensions	Width: 220 mm Depth: 90 mm
Suitable for	Enclosure type: KL
Gland plate	Size: 2
Operating temperature range	-40 °C70 °C

© Rittal 2025

Features

Protection category IP to EN 60 529	IP 55 if correctly installed
Number knockouts	6
	2
	2
Packaging unit	5 pc(s).
Net weight	0.5
Gross weight	0.581
Customs tariff number	73269098
EAN	4028177010901
E-Number Sweden	E3404716
ETIM 9	EC000211
ETIM 8	EC000211
ECLASS 8.0	27142421

© Rittal 2025 3