

Rittal – The System.

Faster – better – everywhere.



KX 1585.000

KX Bus Housings

State: 2026-02-06 (Source: rittal.com/ca-en)



KX 1585.000 - KX Bus Housings Stainless steel

The stainless steel KX bus housing offers easy access with the standard 180° hinges and has a high protection rating of IP66.



Features

Model No.	KX 1585.000
Product description	The small enclosure KX, bus enclosure KX, stainless steel allows for a flexible interior installation and provides easy access with the standard 180° hinges.
Material	Housing: Stainless steel 1.4301 (AISI 304) Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in PU seal Hinge: Die-cast zinc
Surface finish	Housing and cover: Brushed, grain 180 180° hinges: Chrome-plated
Supply includes	Housing with cover 180° hinges Quick-release fasteners including plastic bushings
Protection category NEMA	NEMA 1 NEMA 3R NEMA 4 NEMA 4X NEMA 12
Protection category IP to EN 60 529	IP 66

Features

Type rating according to UL 50E	Type 1 Type 3R Type 4 Type 4X Type 12
Dimensions	Width: 400 mm Height: 200 mm Depth: 120 mm
Material thickness - cover	1.25 mm
Material thickness - enclosure	1.25 mm
Base material	Stainless steel 1.4301 (AISI 304)
Packaging unit	1 pc(s).
Net weight	3.2
Gross weight	3.46
Customs tariff number	84879059
EAN	4028177919112
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

Approvals

Approvals	Bureau Veritas C-UL DNV-GL Lloyds Register of Shipping
Explanations	Declaration of conformity