

Rittal – The System.

Faster – better – everywhere.



KX 1586.000 KX Bus Housings

State: 2026-02-14 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))



FRIEDHELM LOH GROUP

KX 1586.000 - KX Bus Housings Stainless steel

The stainless steel KX bus housing offers easy access with the standard 180° hinges and has a high protection rating of IP66.



Features

| | |
|-------------------------------------|---|
| Model No. | KX 1586.000 |
| Product description | The small enclosure KX, bus enclosure KX, stainless steel allows for a flexible interior installation and provides easy access with the standard 180° hinges. |
| Material | Housing: Stainless steel 1.4301 (AISI 304) Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in PU seal Hinge: Die-cast zinc |
| Surface finish | Housing and cover: Brushed, grain 180 180° hinges: Chrome-plated |
| Supply includes | Housing with cover 180° hinges Quick-release fasteners including plastic bushings |
| Protection category NEMA | NEMA 1 NEMA 3R NEMA 4 NEMA 4X NEMA 12 |
| Protection category IP to EN 60 529 | IP 66 |

Features

| | |
|---------------------------------|---|
| Type rating according to UL 50E | Type 1 Type 3R Type 4 Type 4X Type 12 |
| Dimensions | Width: 600 mm Height: 200 mm Depth: 120 mm |
| Material thickness - cover | 1.25 mm |
| Material thickness - enclosure | 1.25 mm |
| Base material | Stainless steel 1.4301 (AISI 304) |
| Packaging unit | 1 pc(s). |
| Net weight | 4.891 |
| Gross weight | 4.894 |
| Customs tariff number | 84879059 |
| EAN | 4028177919129 |
| ETIM 9 | EC000261 |
| ETIM 8 | EC000261 |
| ECLASS 8.0 | 27180101 |

Approvals

| | |
|--------------|---|
| Approvals | Bureau Veritas C-UL DNV-GL Lloyds Register of Shipping |
| Explanations | Declaration of conformity |
