

Rittal – The System.

Faster – better – everywhere.



SZ 1590.010

Wall mounting bracket

State: 2025-08-05 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 1590.010 - Wall mounting bracket for AX carbon steel, KX carbon steel, AX IT EL

For mounting AX and KX carbon steel enclosures.

Features

Model No.	SZ 1590.010
Product description	For mounting AX and KX carbon steel housings.
Benefits	Screw-fastened directly from the rear with a self-tapping screw into the enclosure eyelet
Material	Carbon steel, zinc-plated
Supply includes	Assembly components
Wall distance	10 mm
Suitable for	Enclosure type: AX carbon steel KX carbon steel AX wall-mounted housing, 3-part
Type rating according to UL 50E	Type 1 Type 3R Type 4 Type 12
Packaging unit	4 pc(s).
Net weight	0.132
Gross weight	0.168
PCF/VE (cradle-to-gate)	0.5 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	83025000
EAN	4028177938045
E-Number Sweden	E3465246
ETIM 9	EC002625

Features

ETIM 8	EC002625
ECLASS 8.0	27189234

Approvals

Approvals	DNV-GL UL + C-UL - FTTA
-----------	----------------------------