

Rittal – The System.

Faster – better – everywhere.



DK 2094.400 Slot-in cable gland, 482.6 mm (19")

State: 2026-05-22 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 2094.400 - Slot-in cable gland, 482.6 mm (19")

Consist of an expanding nut which is inserted into the square hole at the front and then secured with the fastening screw.



Features

| | |
|---------------------|---|
| Model No. | DK 2094.400 |
| Version | Size of mounting hole 9.5 x 9.5 mm |
| Product description | The screw fastening consists of an expanding nut which is inserted into the square hole at the front only and then secured with the fastening screw. When the screw is tightened the captive nut expands in this way securing the elements. Holder tightening zone 1.2 – 4.5 mm. Multi-tooth screw head, bit size T 30. |
| Material | Carbon steel |
| Surface finish | Zinc-plated |
| Supply includes | Flat-head screw Expanding nuts Plastic washers |
| Dimensions | Thread: M6 Thread length: 16 mm |
| Packaging unit | 50 pc(s). |

Features

| | |
|-------------------------------------|--|
| Net weight | 0.3 kg |
| Gross weight | 0.38 kg |
| PCF/VE (cradle-to-gate) | 1.3 kg CO2 eq (Cat B) |
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number | 73181900 |
| ETIM 9 | EC002358 |
| ETIM 8 | EC002358 |
| ECLASS 8.0 | 23110815 |
| Product description | DK Slot-in cable gland, 482.6 mm (19"), M6, L: 16 mm |