### Rittal - The System.

Faster – better – everywhere.





SR 2345.700

# Pivoting Frame, large, without trim panel

State: 2025-11-16 (Source: rittal.com/ca-en)



## SR 2345.700 - Pivoting Frame, large, without trim panel for TS, VX SE, 600 mm and 1200 mm wide enclosures

For 600 mm and 1200 mm wide enclosures, 22 - 45 U, without trim panel, to mount 482.6 mm (19") equipment.





#### **Features**

Model No.	SR 2345.700
Product description	To mount 482.6 mm (19") equipment.
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Cam with double-bit lock insert Parts for attaching to the installation kit
Mounting tip	Depending on the installation situation TS punched sections with mounting flange, 23 x 73 mm, or TS punched sections with mounting flange, 17 x 73 mm are required
Note	See "Technical Details" for other expansion options
Suitable for	Enclosure type: TS Width: = 600 mm
	= 1,200 mm Height: ≥ 2,200 mm
Height units	
Height units Suitable for enclosure type	Height: ≥ 2,200 mm
	Height: ≥ 2,200 mm 45 U

© Rittal 2025 2

### **Features**

Gross weight	14.003
Customs tariff number	94039910
EAN	4028177021785
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189261

© Rittal 2025 3