

Rittal – The System.

Faster – better – everywhere.



SG 2368.000 Connection element

State: 2026-04-06 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SG 2368.000 - Connection element for signal pillar, modular

Optionally for conduit or wall/base mounting, with cover for optical components.

Features

Model No.	SG 2368.000
Version	for conduit mounting
Product description	Optionally for conduit or wall/base mounting. Screw terminals in the connection component. With cover for optical components. Contact hazard protection to VDE.
Benefits	Easy mounting and contact via bayonet fastener.
Function principle	A modular layout is possible with connection, optical and acoustic components, incandescent lamps and a label panel.
Material	Housing of polyamide
Color	Black
Diameter	70 mm
Rated impulse withstand voltage, phase to phase	2500 V AC
Rated insulation voltage	250 V AC
Signal pillar	modular
Dimensions	Height: 43 mm
Protection category IP to EN 60529	IP 54
Rated operating voltage	12 V - 240 V (AC/DC)
Packaging unit	1 pc(s).
Net weight	0.11 kg
Gross weight	0.115 kg
Customs tariff number	85369095

Features

ECLASS 8.0

27371232

Product description

SG Connection element, for signal pillar, modular, for conduit mounting

Approvals

Approvals

UL + C-UL (listed)
UR