


# Rittal – The System.

Faster – better – everywhere.



## SG 2368.000 Connection element

State: 2025-12-21 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SG 2368.000 - Connection element for signal pillar, modular

Optionally for conduit or wall/base mounting, with cover for optical components.

## Features

Model No.	SG 2368.000
Version	for conduit mounting
Product description	Optionally for conduit or wall/base mounting. Screw terminals in the connection component. With cover for optical components. Contact hazard protection to VDE.
Benefits	Easy mounting and contact via bayonet fastener.
Function principle	A modular layout is possible with connection, optical and acoustic components, incandescent lamps and a label panel.
Material	Housing of polyamide
Color	Black
Diameter	70 mm
Rated impulse withstand voltage, phase to phase	2500 V AC
Rated insulation voltage	250 V AC
Signal pillar	modular
Dimensions	Height: 43 mm
Protection category IP to EN 60529	IP 54
Rated operating voltage	12 V - 240 V (AC/DC)
Packaging unit	1 pc(s).
Net weight	0.11
Gross weight	0.115
Customs tariff number	85369095

# Features

EAN	4028177219908
ECLASS 8.0	27371232

# Approvals

Approvals	UL + C-UL (listed) UR
-----------	--------------------------