

Rittal – The System.

Faster – better – everywhere.



SG 2368.010 Connection element

State: 2026-04-05 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SG 2368.010 - Connection element for signal pillar, modular

Optionally for conduit or wall/base mounting, with cover for optical components.

Features

Model No.	SG 2368.010
Version	for wall/base mounting
Product description	Optionally for conduit or wall/base mounting. Screw terminals in the connection component. With cover for optical components. Contact hazard protection to VDE.
Benefits	Easy mounting and contact via bayonet fastener.
Function principle	A modular layout is possible with connection, optical and acoustic components, incandescent lamps and a label panel.
Material	Housing of polyamide
Color	Black
Diameter	70 mm
Rated impulse withstand voltage, phase to phase	2500 V AC
Rated insulation voltage	250 V AC
Signal pillar	modular
Dimensions	Height: 43 mm
Protection category IP to EN 60529	IP 54
Rated operating voltage	12 V - 240 V (AC/DC)
Packaging unit	1 pc(s).
Net weight	0.11 kg
Gross weight	0.123 kg
Customs tariff number	85369095

Features

ECLASS 8.0

27371232

Product description

SG Connection element, for signal pillar, modular, for wall/base mounting

Approvals

Approvals

UL + C-UL (listed)
UR