

**Rittal – The System.**

Faster – better – everywhere.



**SG 2369.010**

**Steady light component**

State: 2026-01-30 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# SG 2369.010 - Steady light component for signal pillar, modular

With 360° signal transmission thanks to optimized prism system, no. of potential stages = 5 components, with identical voltage.

## Features

|   |   |
|---|---|
| Model No.                                       | SG 2369.010   |
| Version   | Steady light component  |
| Product description                             | With 360° signal transmission thanks to optimized prism system.<br>Number of potential stages = 5 components, with identical voltage.   |
| Benefits  | Easy mounting and contact via bayonet fastener.<br>Configuration of up to five components with the same voltage.<br>Components are available in a range of colors and voltages. |
| Function principle                              | A modular layout is possible with connection, optical and acoustic components, incandescent lamps and a label panel.  |
| Material  | Housing of polyamide<br>Cap: Transparent polycarbonate  |
| Color   | Green   |
| Diameter  | 70 mm   |
| Rated impulse withstand voltage, phase to phase | 2500 V AC   |
| Rated insulation voltage                        | 250 V AC  |
| Note on Model No.:                              | Incandescent lamps not included with the supply.  |
| Dimensions                                      | Height: 56 mm   |
| Protection category IP to EN 60 529             | IP 54 if a cover or acoustic component is fitted at the top   |
| Rated operating voltage                         | 12 V - 240 V (AC/DC)  |
| Packaging unit                                  | 1 pc(s).  |
| Net weight                                      | 0.07  |

# Features

---

|                       |               |
|-----------------------|---------------|
| Gross weight          | 0.087         |
| Customs tariff number | 85311095      |
| EAN                   | 4028177219939 |
| ECLASS 8.0            | 27371220      |

# Approvals

---

|           |                          |
|-----------|--------------------------|
| Approvals | UL + C-UL (listed)<br>UR |
|-----------|--------------------------|