


# Rittal – The System.

Faster – better – everywhere.



## SG 2370.171

### LED steady light component

State: 2025-07-15 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SG 2370.171 - LED steady light component for signal pillar, modular

With 360° signal transmission due to optimized prism system.

## Features

|                                     |   |
|-------------------------------------|---|
| Model No.                           | SG 2370.171   |
| Version                             | LED steady light component  |
| Benefits                            | With 360° signal transmission thanks to optimized prism system<br>Configuration of up to five components with the same voltage. |
| Function principle                  | A modular layout is possible with connection, optical and acoustic components and a label panel                                 |
| Material                            | Housing of polyamide<br>Cap: Transparent polycarbonate  |
| Color                               | Yellow  |
| Protection category IP to EN 60 529 | IP 65, when cover or acoustic component is mounted on top   |
| Rated operating voltage             | 230 V   |
| Packaging unit                      | 1 pc(s).  |
| Net weight                          | 0.072   |
| Gross weight                        | 0.073   |
| Customs tariff number               | 85311095  |
| EAN                                 | 4028177953611   |
| ETIM 9                              | EC000232  |
| ETIM 8                              | EC000232  |
| ECLASS 8.0                          | 27371220  |

# Approvals

|              |                           |
|--------------|---------------------------|
| Approvals    | UL + C-UL (listed)        |
| Explanations | Declaration of conformity |