

Rittal – The System.

Faster – better – everywhere.



SG 2370.541

LED flashing light component

State: 2026-02-10 (Source: rittal.com/ca-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SG 2370.541 - LED flashing light component for signal pillar, modular

With 360° signal transmission due to optimized prism system.

Features

Model No.	SG 2370.541
Version	LED flashing light component
Benefits	<p>Easy mounting and contact via bayonet fastener.</p> <p>With 360° signal transmission thanks to optimized prism system</p> <p>Configuration of up to five components with the same voltage.</p> <p>Components are available in a range of colors and voltages.</p>
Function principle	A modular layout is possible with connection, optical and acoustic components and a label panel
Material	Housing of polyamide Cap: Transparent polycarbonate
Color	Blue
Protection category IP to EN 60 529	IP 65, when cover or acoustic component is mounted on top
Rated operating voltage	24 V (AC/DC)
Packaging unit	1 pc(s).
Net weight	0.072
Gross weight	0.073
Customs tariff number	85311095
EAN	4028177953666
ETIM 9	EC000232
ETIM 8	EC000232
ECLASS 8.0	27371220

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity
