

Rittal – The System.

Faster – better – everywhere.



SG 2376.030

Acoustic component

State: 2025-07-02 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SG 2376.030 - Acoustic component for signal pillar, modular

To indicate warnings or malfunctions.

Features

| | |
|---|--|
| Model No. | SG 2376.030 |
| Version | Volume and 8 tones may be set, 100 dB, max. 25 mA |
| Product description | To indicate warnings or malfunctions. |
| Benefits | Easy mounting and contact via bayonet fastener. |
| Applications | Mounting only on the upper end of the optical components or directly on the connection component |
| Function principle | A modular layout is possible with connection, optical and acoustic components, incandescent lamps and a label panel. |
| Material | Housing of polyamide |
| Color | Black |
| Rated impulse withstand voltage, phase to phase | 2500 V AC |
| Rated insulation voltage | 250 V AC |
| Packaging unit | 1 pc(s). |
| Net weight | 0.11 |
| Gross weight | 0.112 |
| Customs tariff number | 85369095 |
| EAN | 4028177220461 |
| ECLASS 8.0 | 27371237 |

Approvals

Approvals

Approvals

UR