Rittal - The System.

Faster – better – everywhere.





AE 2383.250 Rail for Interior Installation

State: 2025-10-23 (Source: rittal.com/ca-en)



AE 2383.250 - Rail for Interior Installation for AE/WM

Mounted in the housing, no machining required. Suitable for all-round mounting on the sides, base and roof areas.



Features

Model No.	AE 2383.250	
Product description	Mounted in the housing, no machining required. Suitable for all-round mounting on the sides, base and roof areas. Variable, with 2 rows of system punchings, provides additional mounting space for: TS system chassis, enclosure lights, door-operated switch, door stay, cable conduit holder	
Material	Carbon steel	
Surface finish	Zinc-plated	
Note	Other mounting options: Mounting plates, locatable, TS 8612.400 Mounting plates, screw-fastening, large, TS 8612.410 Mounting plates, screw-fastening, small, PS 4532.000 Mounting bracket, PS 4597.000	
Suitable for	Enclosure type: AE Depth: = 250 mm	
Packaging unit	4 pc(s).	
Net weight	0.72	
Gross weight	0.8	
Customs tariff number	73269098	
EAN	4028177687424	
E-Number Sweden	E3404333	

© Rittal 2025

Features

ETIM 9	EC002625	
ETIM 8	EC002625	
ECLASS 8.0	27189234	

© Rittal 2025 3