

Rittal – The System.

Faster – better – everywhere.



SZ 2388.850 Rail

State: 2025-12-08 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE



SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2388.850 - Rail for EMC shielding bracket and strain relief

Combined rails for strain relief and EMC contacting of inserted cables.



Features

Model No.	SZ 2388.850
Version	C rail to accommodate cable clamps T-head slots in 40 mm hole pattern for cable attachment using cable ties
Product description	Combined rails for strain relief and EMC contacting of inserted cables.
Benefits	Additional contacting on the left or right of the rail via existing holes (9 mm diameter) Prepared for tool-free assembly of EMC shielding bracket
Material	Extruded aluminum section
Surface finish	Chrome-free passivated
Supply includes	1 rail 2 retaining brackets Assembly components
Length	753 mm
Installation options	On the horizontal/vertical enclosure section on a mounting plate, may also be fitted without a retaining bracket
Suitable for	Enclosure type: VX TS Width: = 800 mm
Packaging unit	1 pc(s).

Features

Net weight	0.63
Gross weight	0.68
Customs tariff number	76042990
EAN	4028177698925
ETIM 9	EC002625
ETIM 8	EC002625
ECLASS 8.0	27189234