

Rittal – The System.

Faster – better – everywhere.



SZ 2412.310 Grounding Braid

State: 2025-07-11 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2412.310 - Grounding Braid

Tin-plated copper, in various lengths and cross-sections with press-fit contact rings, to counteract the proximity effect at high frequencies, while offering flexible connection options.



Features

Model No.	SZ 2412.310
Product description	Tin-plated copper, in various lengths and cross-sections with press-fit contact rings. Grounding braids counteract the proximity effect at high frequencies, while offering flexible connection options.
Cross-section	10 mm ²
Connection	M6 – M6
Note	Please refer to the installation instructions or equipment grounding conductor brochure of the respective enclosure or housing system.
Dimensions	Length: 300 mm
Packaging unit	10 pc(s).
Net weight	0.3
Gross weight	0.359
Customs tariff number	74198010
EAN	4028177022584
ETIM 9	EC000839
ETIM 8	EC000839
ECLASS 8.0	27062302

Approvals

Approvals

UL + C-UL (listed)