

Rittal – The System.

Faster – better – everywhere.



SZ 2412.325 Grounding Braid

State: 2026-06-05 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2412.325 - Grounding Braid

Tin-plated copper, in various lengths and cross-sections with press-fit contact rings, to counteract the proximity effect at high frequencies, while offering flexible connection options.



Features

Model No.	SZ 2412.325
Product description	Tin-plated copper, in various lengths and cross-sections with press-fit contact rings. Grounding braids counteract the proximity effect at high frequencies, while offering flexible connection options.
Cross-section	25 mm ²
Connection	M8 – M8
Note	Please refer to the installation instructions or equipment grounding conductor brochure of the respective enclosure or housing system.
Dimensions	Length: 300 mm
Packaging unit	10 pc(s).
Net weight	0.75 kg
Gross weight	0.788 kg
Customs tariff number	74198010
ETIM 9	EC000839
ETIM 8	EC000839
ECLASS 8.0	27062302
Product description	SZ Earthing strap, size: M8, for diameter 25 mm ²

Approvals

Approvals

UL + C-UL (listed)