

Rittal – The System.

Faster – better – everywhere.



SZ 2423.000

Spacer

State: 2025-05-04 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2423.000 - Spacer for roof plate

For raising the roof for ventilation purposes, available in three different heights. Not suitable for crane transport.



Features

| | |
|-------------------------------|----------------------------------------------------------------------------------------------------------------|
| Model No. | SZ 2423.000 |
| Product description | For raising the roof for ventilation purposes, available in three different heights. |
| Material | Hexagon steel section |
| Surface finish | Zinc-plated |
| Supply includes | Assembly components |
| Mounting tip | Not suitable for crane transportation |
| Dimensions | Height: 20 mm |
| Dimensions | Thread: M12 |
| Suitable for | Enclosure type: VX TS |
| Packaging unit | 4 pc(s). |
| Net weight | 0.216 |
| Gross weight | 0.255 |
| PCF per pack (cradle-to-gate) | 1 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 83024900 |

Features

| | |
|-----------------|---------------|
| EAN | 4028177022799 |
| E-Number Sweden | E7239675 |
| ETIM 9 | EC002625 |
| ETIM 8 | EC002625 |
| ECLASS 8.0 | 27189234 |